



The multi-hole cushions are available in various combinations of hole sizes and quantities. This unique design allows using a single cushion to easlily manage and fix multiple cables of different sizes. Multi-hole cushions can be installed using popular cable clamps, including snap-in, butterfly, stackable clamps, and cable blocks. The hanger solutions with these multi-hole cushions are very useful in the tower-top cable management for the installation of AISG, fiber, power, hybrid, and coaxial cables with an outer diameter up to 5/8".

**FEATURES / BENEFITS**

- One cushion accommodates multiple cables in different sizes - reduce material and installation costs, save spaces on tower
- Made of UV-resistant EPDM - solution is durable even in extreme environmental conditions
- Versatile design - Fix and manage various cables by one cushion
- Compatible to various types of clamps - support diverse site conditions



**Technical features**

**GENERAL SPECIFICATIONS**

|                                   |    |   |
|-----------------------------------|----|---|
| <b>Product Type</b>               |    | Rubber Cushion, Cable Lining  |
| <b>Configuration</b>              |    | Multi-hole  |
| <b>Color</b>                      |    | Black   |
| <b>Installation Hardware Type</b> |    | Snap-in Clamp, Stackable Snap-in Clamp, Butterfly Clamp, Clip-on Clamp, Cable block |
| <b>Compatible Clamp Size</b>      | in | 1-5/8"  |

**MECHANICAL SPECIFICATIONS**

|   |  |             |
|---|--|-------------|
| <b>Material</b>                         |  | EPDM Rubber |
| <b>Number of Cable / Waveguide Runs</b> |  | 10          |
| <b>Amount of Hole Type 1</b>            |  | 10          |

**TEMPERATURE SPECIFICATIONS**

|                                 |         |                         |
|---------------------------------|---------|-------------------------|
| <b>Installation Temperature</b> | °C (°F) | 0 to 30 (32 to 86 )     |
| <b>Operation Temperature</b>    | °C (°F) | -25 to 75 (-13 to 167 ) |
| <b>Storage Temperature</b>      | °C (°F) | -10 to 25 (14 to 77 )   |

**PACKAGING INFORMATION**

|                         |         |             |
|-------------------------|---------|-------------|
| <b>Package Quantity</b> |         | 10          |
| <b>Weight per kit</b>   | kg (lb) | 1.17 (2.58) |



### CUSH-10-S14-158

Cushion with 10 Holes, for 5-7mm Cables, Compatible with 1-5/8" Clamps

#### RELATED PRODUCTS

| MULTI-HOLE CUSHION SPECIFICATIONS       |                     |                               |                               | COMPATIBLE CLAMP OPTIONS (CLICK MODELS TO SEE DATASHEETS) |                          |                           |
|---|---------------------|-------------------------------|-------------------------------|---|--------------------------|---------------------------|
| Model Number                            | Total Hole Quantity | Cable 1 Quantity x Size Range | Cable 2 Quantity x Size Range | Stackable Snap-in Clamp                                   | Snap-in Clamp            | Butterfly Clamp           |
| <a href="#">CUSH-4-L12-158</a>          | 4                   | 4 x 15 - 17 mm                | N/A                           | <a href="#">SNAP-ST-158</a>                               | <a href="#">SNAP-158</a> | <a href="#">CLAMP-158</a> |
| <a href="#">CUSH-4-S14-2-L12-158</a>    | 6                   | 4 x 6 - 7 mm                  | 2 x 15 - 17 mm                |   |                          |                           |
| <a href="#">CUSH-4-L1438-2-L12-158</a>  | 6                   | 4 x 10 - 11 mm                | 2 x 15 - 17 mm                |   |                          |                           |
| <a href="#">CUSH-4-S14-4-L14S12-158</a> | 8                   | 4 x 6 - 7 mm                  | 4 x 11 - 13 mm                |   |                          |                           |
| <a href="#">CUSH-1-L1438-2-58-158</a>   | 3                   | 1 x 10 - 11 mm                | 2 x 19 - 21 mm                |   |                          |                           |
| <a href="#">CUSH-10-S14-158</a>         | 10                  | 10 x 5 - 7 mm                 | N/A                           |   |                          |                           |
| <a href="#">CUSH-4-S14-4-L1438-158</a>  | 8                   | 4 x 6 - 7 mm                  | 4 x 9 - 11 mm                 |   |                          |                           |
| <a href="#">CUSH-4-S14-2-58-158</a>     | 6                   | 4 x 6 - 7 mm                  | 2 x 20- 22 mm                 |   |                          |                           |
| <a href="#">CUSH-7-L14S38-158</a>       | 7                   | 7 x 9 - 10 mm                 | N/A                           |   |                          |                           |
| <a href="#">CUSH-2-58-158</a>           | 2                   | 2 x 20- 22 mm                 | N/A                           |   |                          |                           |
| <a href="#">CUSH-7-14S38-158</a>        | 7                   | 7 x 4-10 mm                   | N/A                           |   |                          |                           |

\* More cushions and clamps may be available upon request.

External Document Links  
[Installation Instruction](#)

[Notes](#)