



The multi-hole cushions are available in various combinations of hole sizes and quantities. This unique design allows using a single cushion to easlily manage and fix multiple cables of different sizes. Multi-hole cushions can be installed using popular cable clamps, including snap-in, butterfly, stackable clamps, and cable blocks. The hanger solutions with these multi-hole cushions are very useful in the tower-top cable management for the installation of AISG, fiber, power, hybrid, and coaxial cables with an outer diameter up to 5/8".

**FEATURES / BENEFITS**

- One cushion accommodates multiple cables in different sizes - reduce material and installation costs, save spaces on tower
- Made of UV-resistant EPDM - solution is durable even in extreme environmental conditions
- Versatile design - Fix and manage various cables by one cushion
- Compatible to various types of clamps - support diverse site conditions



**Technical features**

**GENERAL SPECIFICATIONS**

<b>Product Type</b>		Rubber Cushion, Cable Lining
<b>Configuration</b>		Multi-hole
<b>Color</b>		Black
<b>Installation Hardware Type</b>		Snap-in Clamp, Stackable Snap-in Clamp, Butterfly Clamp, Clip-on Clamp, Cable block
<b>Compatible Clamp Size</b>	in	1-5/8"

**MECHANICAL SPECIFICATIONS**

<b>Material</b>		EPDM Rubber
<b>Number of Cable / Waveguide Runs</b>		10
<b>Amount of Hole Type 1</b>		10

**TEMPERATURE SPECIFICATIONS**

<b>Installation Temperature</b>	°C (°F)	0 to 30 (32 to 86 )
<b>Operation Temperature</b>	°C (°F)	-25 to 75 (-13 to 167 )
<b>Storage Temperature</b>	°C (°F)	-10 to 25 (14 to 77 )

**PACKAGING INFORMATION**

<b>Package Quantity</b>		10
<b>Weight per kit</b>	kg (lb)	1.17 (2.58)



### CUSH-10-S14-158

Cushion with 10 Holes, for 5-7mm Cables, Compatible with 1-5/8" Clamps

#### RELATED PRODUCTS

MULTI-HOLE CUSHION SPECIFICATIONS				COMPATIBLE CLAMP OPTIONS (CLICK MODELS TO SEE DATASHEETS)		
Model Number	Total Hole Quantity	Cable 1 Quantity x Size Range	Cable 2 Quantity x Size Range	Stackable Snap-in Clamp	Snap-in Clamp	Butterfly Clamp
<a href="#">CUSH-4-L12-158</a>	4	4 x 15 - 17 mm	N/A	<a href="#">SNAP-ST-158</a>	<a href="#">SNAP-158</a>	<a href="#">CLAMP-158</a>
<a href="#">CUSH-4-S14-2-L12-158</a>	6	4 x 6 - 7 mm	2 x 15 - 17 mm			
<a href="#">CUSH-4-L1438-2-L12-158</a>	6	4 x 10 - 11 mm	2 x 15 - 17 mm			
<a href="#">CUSH-4-S14-4-L14S12-158</a>	8	4 x 6 - 7 mm	4 x 11 - 13 mm			
<a href="#">CUSH-1-L1438-2-58-158</a>	3	1 x 10 - 11 mm	2 x 19 - 21 mm			
<a href="#">CUSH-10-S14-158</a>	10	10 x 5 - 7 mm	N/A			
<a href="#">CUSH-4-S14-4-L1438-158</a>	8	4 x 6 - 7 mm	4 x 9 - 11 mm			
<a href="#">CUSH-4-S14-2-58-158</a>	6	4 x 6 - 7 mm	2 x 20- 22 mm			
<a href="#">CUSH-7-L14S38-158</a>	7	7 x 9 - 10 mm	N/A			
<a href="#">CUSH-2-58-158</a>	2	2 x 20- 22 mm	N/A			
<a href="#">CUSH-7-14S38-158</a>	7	7 x 4-10 mm	N/A			

\* More cushions and clamps may be available upon request.

External Document Links  
[Installation Instruction](#)

[Notes](#)